



機種名	$\phi A$	B	(球R) C	(P.C.D.) D	E	F	G	$\phi H$
C2Z1-500L, 1, 2	113	85	50	50	4-M6 深さ10	138	10	M16×1.5
C2F1-500L, 1, 2	98	105	50	50	4-M6 深さ10	120	9	M16×1.0
C2Z1-5, 10	138	110	100	60	4-M8 深さ15	165	15	35
C2F1-5, 10	98	100	100	60	4-M8 深さ15	120	10	24
C2Z1-20	164	145	200	80	4-M12 深さ20	193	20	45
C2F1-20	120	120	150	80	4-M12 深さ20	145	10	36
C2X1-30, 50	138	160	200	80	4-M12 深さ20	165	20	50
C2X1-100	164	190	200	100	4-M16 深さ20	193	30	70
C2X1-200	214	230	300	130	4-M16 深さ20	245	30	95
C2X1-300	214	320	600	130	4-M24 深さ35	245	30	120
C2X1-500	316	400	800	200	6-M30 深さ50	349	30	170